

Smart Vision Lights 45mm Bar Light Mount



Stock **#90-439** NEW **1 In Stock**

-

1

+

S\$96^{.60}

ADD TO CART

Volume Pricing	
Qty 1+	S\$96.60 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

BKT0025

Model Number:

Smart Vision Lights LLC

Manufacturer:

Environmental & Durability Factors

-10° to +40°

Operating Temperature (°C):

Regulatory Compliance

[View](#)

Certificate of Conformance:

PRODUCT DETAILS

- Compact Bar Lights Available In 45mm Or 75mm Lengths
- Delivers up to 73,000 (for the 75mm) and 44,000 (45mm) lux with Strob ing
- Available In White, Blue, Green, Red, Or IR Wavelengths
- Ideal For Space-Constrained Imaging Applications

Smart Vision Lights LMMni Bar Lights are compact linear lights that are designed to deliver intense light for space-constrained applications and feature IP65 rating for dust and water protection. These lights are available in 45 or 75mm lengths in white, blue (470nm), green (530nm), red (635), or IR (850nm) wavelengths. Built in Multi-Drive™ technology allows for these lights to operate in continuous mode for standard operation or strobe mode for high speed or increased brightness needs. Smart Vision Lights LMMni Bar Lights are recommended to use at a working distance of 100 – 1000mm. Optional mounting brackets are sold separately and can be used to configure the lights in a quad formation to illuminate a larger area.