

Universal Right Angle Bracket



Universal Right Angle Bracket (#11-157)

Stock **#11-157** **2 In Stock**

-

1

+

S\$233⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$233.80 each
Need More?	Request Quote

Product Downloads

General

Universal	Type:
-----------	-------

Physical & Mechanical Properties

1.0	Thickness (inches):
6.0	Width (inches):

Black Anodized Aluminum	Construction:
-------------------------	---------------

12.0	Length (inches):
Threading & Mounting	
Mounting Threads:	
(9) 1/4-20 (M6x1.0) S.H.C.S. Thru-Slots	
Regulatory Compliance	
RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	
Reach 250:	
Compliant	

Product Details

- Universal Design Works With Metric and English Bench Plates and Breadboards
- Uses Standard 1/4-20 or M6 Socket Head Cap Screws
- Black Anodized Aluminum Construction

Universal Right Angle Brackets allow our English and Metric Economical Bench Plates to be mounted orthogonally to a Composite Breadboard or another bench plate. These brackets are made from 1" thick black anodized aluminum. Thru-slots on the vertical and horizontal arms of the bracket allow for the use of both M6 and 1/4-20 SHCS for mounting, and accommodate breadboard hole spacing of 1" and 25mm. Universal Right Angle Brackets feature a ubiquitous design that enables easy integration of additional components into any benchtop system. For applications that require more structural support, purchase the Universal Right Angle Bracket, Pair ([#11-158](#)).

Note: Not recommended for use with plates taller than 12" or 300mm.

Technical Information

