

[See all 14 Products in Family](#)

UV-VIS Heavy-Duty Transmission Dip Probe

See More by [Ocean Optics](#)



Stock #90-569 **NEW** 1 In Stock

- 1 + \$3,241.⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	\$3,241.00 each
Need More?	Request Quote

Product Downloads

Fiber Connector Type:

SMA905

General

Model Number:

T1300-UV-VIS

Note:

Breakout 1 meter from end of the probe

Title:

UV-VIS Heavy-Duty Transmission Dip Probe

Optical Properties

Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**

Compliant **Reach 250:**

Product Details

- Transmission Dip Probes Designed for Reliable In-Solution Absorbance/Transmission Measurements
- Rugged Stainless Steel or PEEK for Tough Process Conditions and Harsh Environments
- Flexible Path Lengths Available with Interchangeable Probe Tips
- Compatible with Ocean Optics Spectrometers and Accessories

Ocean Optics Transmission Dip Probes couple to spectrometers and light sources to measure absorbance and transmission in solutions. Choose from ruggedized high-pressure probe ([#90-569](#)) for demanding process environments or PEEK-jacketed probes ([#90-570](#) and [#90-571](#)) for harsh chemical conditions, spanning UV–VIS to VIS–NIR wavelengths. Easily customize your setup with accessories such as interchangeable probe tips in various path lengths and the protective sleeve ([#90-585](#)) for extended durability in corrosive or high-temperature applications. Ocean Optics Transmission Dip Probes are designed for seamless integration with [Ocean Optics spectroscopy systems and compatible accessories](#).

Technical Information

Transmission Dip Probe	Transmission Dip Probe Stock Number	Compatible Transmission Dip Probe Tip	Compatible Transmission Dip Probe Tip Stock Number
UV-VIS Heavy-Duty Transmission Dip Probe	#90-569	Harsh Environment Transmission Dip Probe Tip, 2 mm	#90-582
		Harsh Environment Transmission Dip Probe Tip, 5 mm	#90-584
		Harsh Environment Transmission Dip Probe Tip, 10 mm	#90-580
		Harsh Environment Transmission Dip Probe Tip, 25 mm	#90-581
		Harsh Environment Transmission Dip Probe Tip, 50 mm	#90-583
UV-VIS Transmission Dip Probe	#90-570	Stainless Steel Transmission Dip Probe Tip, 2 mm	#90-573
		Stainless Steel Transmission Dip Probe Tip, 5 mm	#90-576
		Stainless Steel Transmission Dip Probe Tip, 10 mm	#90-572
		Adjustable Path Length Transmission Dip Probe Tip, 2–10 mm	#90-578
		Adjustable Path Length Transmission Dip Probe Tip, 10–20 mm	#90-577
VIS-NIR Transmission Dip Probe	#90-571	Stainless Steel Transmission Dip Probe Tip, 2 mm	#90-573
		Stainless Steel Transmission Dip Probe Tip, 5 mm	#90-576
		Stainless Steel Transmission Dip Probe Tip, 10 mm	#90-572
		Adjustable Path Length Transmission Dip Probe Tip, 2–10 mm	#90-578
		Adjustable Path Length Transmission Dip Probe Tip, 10–20 mm	#90-577

