

[See all 33 Products in Family](#)

TECHSPEC® UV-VIS ND Filter Kit, 25mm Diameter Filters



Stock #47-511 **1 In Stock**

⊖ 1 ⊕ \$S\$1,176⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	\$S\$1,176.00 each
Need More?	Request Quote

Product Downloads

General

Filters Included :
0.3, 0.5, 1.0, 1.3, 1.5, 2.0, 2.5, 3.0

Type:
Neutral Density Filter

Physical & Mechanical Properties

Diameter (mm):
25.00

Optical Properties

Substrate: □

Fused Silica (Corning 7980)

Coating:

Metallic Based ND

Blocking Wavelength Range (nm):

250 - 700

Wavelength Range (µm):

0.25 - 0.7

Regulatory Compliance

Certificate of Conformance:

[View](#)

Product Details

- Ideal for 250-700nm Sources
- Optical Densities Ranging from 0.3 to 3.0

TECHSPEC® UV-VIS Neutral Density (ND) Filters are spectrally flat from 250 to 700nm and feature outstanding parallelism and surface characteristics. This combination of high tolerance and broadband performance makes these filters ideal for attenuating a wide range of sources. The filters are suitable for low power laser applications and can be stacked to obtain a variety of optical densities. TECHSPEC UV-VIS Neutral Density (ND) should have their mirrored side oriented toward the source at a 0° angle of incidence. Optical Densities of 0.5, 1.0, 1.5, 2.0, 2.5 and 3.0 available in a [Pre-Loaded Filter Wheel](#).

Note: Due to supply chain issues, our kits may be delivered with an alternative packaging solution in place of a wooden box. For any questions, please contact kits@edmundoptics.com.

TECHSPEC® UV-VIS Reflective Neutral Density Filter Kit

Each kit includes 8 filters in optical density values of 0.3, 0.5, 1.0, 1.3, 1.5, 2.0, 2.5, and 3.0. The kit is ideal for determining precise system optical density requirements. Custom densities are available for OEM applications.