

25.4mm Dia., 4mm Thick, 30' Wedge, Zinc Selenide (ZnSe) Wedged Window | ZC-WW-25-4

See More by [ISP Optics](#)



Stock #16-812 3-5 DAYS

− 1 + **S\$837.38**

ADD TO CART

Qty 1+

S\$837.38

Volume Pricing

[Request Quote](#)

Get Product Downloads



Bevel:
Protective as needed

Clear Aperture (%):
85

Clear Aperture CA (mm):
21.59

Diameter (mm):
25.40 +0.00/-0.13

Thickness (mm):
4.00 ±0.13

Coating:
Uncoated

Coefficient of Thermal Expansion CTE (10⁻⁶/°C):
7.1

Density (g/cm³):
5.27

Edges:
Fine Ground

Index of Refraction n_d:
2.4

Knoop Hardness (kg/mm²):
120

Poisson's Ratio:
0.28

Substrate:
Zinc Selenide (ZnSe)

Surface Flatness (P-V):
2λ @ 633nm

Surface Quality:
60-40

Type:
Protective Window

Wavelength Range (nm):
600 - 18000

Young's Modulus (GPa):
67.2

Wedge Angle:
30' ±15

Model Number:
ZC-VW-25-4

Regulatory Compliance

RoHS:
[Compliant](#)

Certificate of Conformance:
[View](#)