SCHOTT RG665, 12.5mm Dia., 1mm Thick, Colored Glass Longpass Filter

See More by SCHOTT Optical Components

Stock **#16-422** 3-5 DAYS

- 1 + **S$46.40**

ADD TO CART

Qty 1-10
S$46.40

Qty 11+
S$40.60

Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
12.50

Cut-On Wavelength (nm):
665.00 ±6

Density (g/cm^3):

2.77

Glass/Filter Number:
SCHOTT RG665

Coating:
Uncoated

Color:
Red

Passband Limit 1 λ_{p1} (nm):
750

Index of Refraction n_d:
1.54

Spectral Transmittance t_{ip} (%):
96

Stopband Limit λ_s(nm):
580

Surface Quality:
60-40

Transformation Temperature (°C):
527

Thickness (mm):
1.00 ±0.1

Type:
Longpass Filter

Wavelength:
VIS

Dimensional Tolerance (mm):
±0.2

Reflection Factor P_d:
0.91

Bevel:
Protective as needed

Regulatory Compliance

Certificate of Conformance:
View