85 x 50mm English Base Plate

Stock **#58-998** **20+ In Stock**

- 1 + **S$48.30**

ADD TO CART

Volume Pricing	
Qty 1+	**S$48.30** each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Type:	English

Physical & Mechanical Properties

Length (mm):	85.00

Width (mm):	50.00
Thickness (mm):	7.00
Construction:	Black Anodized Aluminum
Number of Slots:	6

Threading & Mounting

Mounting Threads:	(4) 8-32, (5) ¼-20

Regulatory Compliance

RoHS 2015:	Compliant
Certificate of Conformance:	View
Reach 250:	Compliant

PRODUCT DETAILS

- Two Size Options
- Two Platform Options: English or Metric
- English: Four #8-32 holes on½" Square and Four ¼-20 Holes on 1" Square
- Metric: Four M4 x 0.7 holes on 12.5mm Square and Four M6 x 1 Holes on 25mm Square
- Anodized Aluminum Construction

Base Plates have Metric or English threaded holes and additional center trapped hole (M6 x 1 or ¼-20). Base Plates also have extended center slots that ensure full use on matching metric or English breadboard patterns. 85mm x 50mm Base Plates have same tapped holes and slots as 60mm x 35mm Base Plates, but with extra short slots for added flexibility.

TECHNICAL INFORMATION





Units: mm