

[All Products](#) / [Optics](#) / [Optical Mirrors](#) / [Focusing \(Concave\) Mirrors](#)

TECHSPEC® Precision Parabolic Mirrors



- $\lambda/8$ Surface Accuracy
- Wide Range of Sizes up to 412.8mm Diameter
- Variety of Coating Options Offered

Common Specifications

Physical & Mechanical Properties


Back Surface:	Ground
---------------	--------

Optical Properties

Surface Quality:	60-40
------------------	-------

Surface Accuracy:	$\lambda/8$
-------------------	-------------

Technical Information



Products

Surface Accuracy	Dia. (mm)	EFL (mm)	Aperture (f/#)	Coating	Stock Number	Price	Buy
$\lambda/8$	76.20	444.50	f/5.8	Uncoated	#32-064-000	S\$631.40 Volume Pricing	20+ In Stock
$\lambda/8$	76.20	444.50	f/5.8	Protected Aluminum (400-2000nm)	#32-064-522	S\$701.40 Volume Pricing	5 In Stock
$\lambda/8$	76.20	444.50	f/5.8	Enhanced Aluminum (450-650nm)	#32-064-533	S\$771.40 Volume Pricing	3 In Stock
$\lambda/8$	76.20	444.50	f/5.8	Protected Gold (700-10000nm)	#32-064-566	S\$813.40 Volume Pricing	2 In Stock
$\lambda/8$	108.00	444.50	f/4.1	Uncoated	#32-065-000	S\$691.60 Volume Pricing	6 In Stock
$\lambda/8$	108.00	444.50	f/4.1	Protected Aluminum (400-2000nm)	#32-065-522	S\$796.60 Volume Pricing	Contact Us
$\lambda/8$	108.00	444.50	f/4.1	Enhanced Aluminum (450-650nm)	#32-065-533	S\$866.60 Volume Pricing	3 In Stock
$\lambda/8$	108.00	444.50	f/4.1	Protected Gold (700-10000nm)	#32-065-566	S\$922.60 Volume Pricing	1 In Stock
$\lambda/8$	108.00	647.70	f/6	Uncoated	#32-066-000	S\$691.60 Volume Pricing	10 In Stock
$\lambda/8$	108.00	647.70	f/6	Protected Aluminum (400-2000nm)	#32-066-522	S\$796.60 Volume Pricing	3 In Stock
$\lambda/8$	108.00	647.70	f/6	Enhanced Aluminum (450-650nm)	#32-066-533	S\$866.60 Volume Pricing	Contact Us

$\lambda/8$	108.00	647.70	f/6	Protected Gold (700-1000nm)	#32-066-566	S\$922.60 Volume Pricing	1 In Stock
$\lambda/8$	108.00	863.60	f/8	Uncoated	#32-067-000	S\$691.60 Volume Pricing	8 In Stock
$\lambda/8$	108.00	863.60	f/8	Protected Aluminum (400-2000nm)	#32-067-522	S\$796.60 Volume Pricing	Contact Us
$\lambda/8$	108.00	863.60	f/8	Enhanced Aluminum (450-650nm)	#32-067-533	S\$866.60 Volume Pricing	5 In Stock
$\lambda/8$	108.00	863.60	f/8	Protected Gold (700-1000nm)	#32-067-566	S\$922.60 Volume Pricing	1 In Stock
$\lambda/8$	152.40	609.60	f/4	Uncoated	#32-069-000	S\$1,085.00 Volume Pricing	14 In Stock
$\lambda/8$	152.40	609.60	f/4	Protected Aluminum (400-2000nm)	#32-069-522	S\$1,225.00 Volume Pricing	1 In Stock
$\lambda/8$	152.40	609.60	f/4	Enhanced Aluminum (450-650nm)	#32-069-533	S\$1,295.00 Volume Pricing	2 In Stock
$\lambda/8$	152.40	609.60	f/4	Protected Gold (700-1000nm)	#32-069-566	S\$1,470.00 Volume Pricing	2 In Stock
$\lambda/8$	152.40	762.00	f/5	Uncoated	#32-070-000	S\$1,085.00 Volume Pricing	6 In Stock
$\lambda/8$	152.40	762.00	f/5	Protected Aluminum (400-2000nm)	#32-070-522	S\$1,225.00 Volume Pricing	4 In Stock
$\lambda/8$	152.40	762.00	f/5	Enhanced Aluminum (450-650nm)	#32-070-533	S\$1,295.00 Volume Pricing	2 In Stock

λ/8	152.40	762.00	f/5	Protected Gold (700-1000nm)	#32-070-566	S\$1,470.00 Volume Pricing	Contact Us
λ/8	152.40	914.40	f/6	Uncoated	#32-071-000	S\$1,085.00 Volume Pricing	15 In Stock
λ/8	152.40	914.40	f/6	Protected Aluminum (400-2000nm)	#32-071-522	S\$1,225.00 Volume Pricing	Contact Us
λ/8	152.40	914.40	f/6	Enhanced Aluminum (450-650nm)	#32-071-533	S\$1,295.00 Volume Pricing	1 In Stock
λ/8	152.40	914.40	f/6	Protected Gold (700-1000nm)	#32-071-566	S\$1,470.00 Volume Pricing	1 In Stock
λ/8	152.40	1,219.20	f/8	Uncoated	#32-072-000	S\$1,085.00 Volume Pricing	15 In Stock
λ/8	152.40	1,219.20	f/8	Protected Aluminum (400-2000nm)	#32-072-522	S\$1,225.00 Volume Pricing	4 In Stock
λ/8	152.40	1,219.20	f/8	Enhanced Aluminum (450-650nm)	#32-072-533	S\$1,295.00 Volume Pricing	5 In Stock
λ/8	152.40	1,219.20	f/8	Protected Gold (700-1000nm)	#32-072-566	S\$1,470.00 Volume Pricing	2 In Stock
λ/8	203.20	1,016.00	f/5	Uncoated	#32-073-000	S\$1,512.00 Volume Pricing	3 In Stock
λ/8	203.20	1,016.00	f/5	Protected Aluminum (400-2000nm)	#32-073-522	S\$1,722.00 Volume Pricing	1 In Stock
λ/8	203.20	1,016.00	f/5	Enhanced Aluminum (450-650nm)	#32-073-533	S\$1,827.00 Volume Pricing	1 In Stock

λ/8	203.20	1,016.00	f/5	Protected Gold (700-1000nm)	#32-073-566	S\$2,002.00 Volume Pricing	Contact Us
λ/8	203.20	1,219.20	f/6	Uncoated	#32-074-000	S\$1,512.00 Volume Pricing	Contact Us
λ/8	203.20	1,219.20	f/6	Protected Aluminum (400-2000nm)	#32-074-522	S\$1,722.00 Volume Pricing	Contact Us
λ/8	203.20	1,219.20	f/6	Enhanced Aluminum (450-650nm)	#32-074-533	S\$1,827.00 Volume Pricing	Contact Us
λ/8	203.20	1,219.20	f/6	Protected Gold (700-1000nm)	#32-074-566	S\$2,002.00 Volume Pricing	Contact Us
λ/8	203.20	1,625.60	f/8	Uncoated	#32-075-000	S\$1,512.00 Volume Pricing	10 In Stock
λ/8	203.20	1,625.60	f/8	Protected Aluminum (400-2000nm)	#32-075-522	S\$1,722.00 Volume Pricing	Contact Us
λ/8	203.20	1,625.60	f/8	Enhanced Aluminum (450-650nm)	#32-075-533	S\$1,827.00 Volume Pricing	Contact Us
λ/8	203.20	1,625.60	f/8	Protected Gold (700-1000nm)	#32-075-566	S\$2,002.00 Volume Pricing	4 In Stock
λ/8	203.20	2,032.00	f/10	Uncoated	#32-076-000	S\$1,512.00 Volume Pricing	6 In Stock
λ/8	203.20	2,032.00	f/10	Protected Aluminum (400-2000nm)	#32-076-522	S\$1,722.00 Volume Pricing	Contact Us
λ/8	203.20	2,032.00	f/10	Enhanced Aluminum (450-650nm)	#32-076-533	S\$1,827.00 Volume Pricing	Contact Us

λ/8	203.20	2,032.00	f/10	Protected Gold (700-1000nm)	#32-076-566	S\$2,002.00 Volume Pricing	1 In Stock
λ/8	254.00	1,524.00	f/6	Uncoated	#32-274-000	S\$3,675.00 Volume Pricing	4 In Stock
λ/8	254.00	1,524.00	f/6	Protected Aluminum (400-2000nm)	#32-274-522	S\$4,025.00 Volume Pricing	Contact Us
λ/8	254.00	1,524.00	f/6	Enhanced Aluminum (450-650nm)	#32-274-533	S\$4,165.00 Volume Pricing	Contact Us
λ/8	254.00	1,524.00	f/6	Protected Gold (700-1000nm)	#32-274-566	S\$4,340.00 Volume Pricing	3 In Stock
λ/8	254.00	2,032.00	f/8	Uncoated	#32-275-000	S\$3,675.00 Volume Pricing	Contact Us
λ/8	254.00	2,032.00	f/8	Protected Aluminum (400-2000nm)	#32-275-522	S\$4,025.00 Volume Pricing	Contact Us
λ/8	254.00	2,032.00	f/8	Enhanced Aluminum (450-650nm)	#32-275-533	S\$4,165.00 Volume Pricing	2 In Stock
λ/8	254.00	2,032.00	f/8	Protected Gold (700-1000nm)	#32-275-566	S\$4,340.00 Volume Pricing	Contact Us
λ/8	254.00	2,540.00	f/10	Uncoated	#35-726-000	S\$3,675.00 Volume Pricing	3 In Stock
λ/8	254.00	2,540.00	f/10	Protected Aluminum (400-2000nm)	#35-726-522	S\$4,025.00 Volume Pricing	Contact Us
λ/8	254.00	2,540.00	f/10	Enhanced Aluminum (450-650nm)	#35-726-533	S\$4,165.00 Volume Pricing	7 In Stock

λ/8	254.00	2,540.00	f/10	Protected Gold (700-1000nm)	#35-726-566	S\$4,340.00 Volume Pricing	1 In Stock
λ/8	317.50	1,905.00	f/6	Uncoated	#32-276-000	S\$5,110.00 Volume Pricing	2 In Stock
λ/8	317.50	1,905.00	f/6	Protected Aluminum (400-2000nm)	#32-276-522	S\$5,670.00 Volume Pricing	1 In Stock
λ/8	317.50	1,905.00	f/6	Enhanced Aluminum (450-650nm)	#32-276-533	S\$5,775.00 Volume Pricing	Contact Us
λ/8	317.50	1,905.00	f/6	Protected Gold (700-1000nm)	#32-276-566	S\$5,950.00 Volume Pricing	Contact Us
λ/8	317.50	2,540.00	f/8	Uncoated	#32-277-000	S\$5,110.00 Volume Pricing	9 In Stock
λ/8	317.50	2,540.00	f/8	Protected Aluminum (400-2000nm)	#32-277-522	S\$5,670.00 Volume Pricing	Contact Us
λ/8	317.50	2,540.00	f/8	Enhanced Aluminum (450-650nm)	#32-277-533	S\$5,775.00 Volume Pricing	1 In Stock
λ/8	317.50	2,540.00	f/8	Protected Gold (700-1000nm)	#32-277-566	S\$5,950.00 Volume Pricing	1 In Stock
λ/8	317.50	3,175.00	f/10	Uncoated	#35-730-000	S\$5,110.00 Volume Pricing	2 In Stock
λ/8	317.50	3,175.00	f/10	Protected Aluminum (400-2000nm)	#35-730-522	S\$5,670.00 Volume Pricing	1 In Stock
λ/8	317.50	3,175.00	f/10	Enhanced Aluminum (450-650nm)	#35-730-533	S\$5,775.00 Volume Pricing	2 In Stock

$\lambda/8$	317.50	3,175.00	f/10	Protected Gold (700-1000nm)	#35-730-566	S\$5,950.00 Volume Pricing	1 In Stock
$\lambda/8$	412.80	2,032.00	f/4.9	Uncoated	#32-725-000	S\$12,488.00 Volume Pricing	Contact Us
$\lambda/8$	412.80	2,032.00	f/4.9	Protected Aluminum (400-2000nm)	#32-725-522	S\$13,468.00 Volume Pricing	Contact Us
$\lambda/8$	412.80	2,032.00	f/4.9	Enhanced Aluminum (450-650nm)	#32-725-533	S\$13,608.00 Volume Pricing	Contact Us
$\lambda/8$	412.80	2,032.00	f/4.9	Protected Gold (700-1000nm)	#32-725-566	S\$14,658.00 Volume Pricing	Contact Us



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com