

[See all 57 Products in Family](#)

TECHSPEC<sup>®</sup>

40mm Diameter, T-Mount Thick Optic Mount



Stock #57-978 5 In Stock

-

1

+

S\$100<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-4        | S\$100.80 each                |
| Qty 5-9        | S\$89.74 each                 |
| Qty 10-25      | S\$83.02 each                 |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General             |                 |
|---------------------|-----------------|
| Fixed               | Type:           |
| Circular            | Type of Optics: |
| Optic Mount (Fixed) | Function:       |

Physical & Mechanical Properties

|                                   |                                           |
|-----------------------------------|-------------------------------------------|
| 25.0                              | Extension Length (mm):                    |
| Black Anodized Aluminum (6061 T6) | Construction:                             |
| 28.45                             | Total Length (mm):                        |
| 48.0                              | Outer Diameter (mm):                      |
| 38.0                              | Clear Aperture CA (mm):                   |
| 20.95                             | Max. Thickness of Compatible Optics (mm): |
| 5.0                               | Min. Thickness of Compatible Optics (mm): |

Threading & Mounting

|         |                                     |
|---------|-------------------------------------|
| 40.0    | Diameter of Compatible Optics (mm): |
| T-Mount | Thread Type:                        |

Regulatory Compliance

|           |                             |
|-----------|-----------------------------|
| Compliant | RoHS 2015:                  |
| View      | Certificate of Conformance: |
| Compliant | REACH 241:                  |

Product Details

• Mounts for Simple Lenses, Achromats, Filters, or Reticles

• Designed to Integrate with Any C, S, or T-Mount Components

• Optic is Held in Place with Included Retaining Ring

TECHSPEC® C, S, and T-Mount Circular Optic Mounts are designed to mount a variety of circular optical components into C, S, or T-Mount compatible systems. An included threaded retainer ring, designed to accept a standard spanner wrench, securely holds the optical component. These circular optic mounts are compatible with a wide variety of Edmund Optics optomechanical components utilizing C, S, or T-Mount threads, such as [extension tubes](#) and [kinematic mounts](#). TECHSPEC® C, S, and T-Mount Circular Optic Mounts are threaded for 1" x 32TPI, M12 x 0.5, or M42 x 0.75 mounting, with 30mm, 16mm, and 48mm outer diameters, respectively. These mounts are ideal for creating and personalization of a diverse range of optical systems.

**Note:** [#56-353](#), [#56-354](#), [#52-933](#), and [#52-292](#) are all 3-part assemblies

Technical Information

