

# 50mm, Mounting Cell



50mm, Mounting Cell, #55-009

Stock **#55-009** 20+ In Stock

-

1

+

S\$38<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | S\$38.09 each                 |
| Qty 10-25      | S\$34.35 each                 |
| Qty 26-49      | S\$32.56 each                 |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

## SPECIFICATIONS

General

Type:

Fixed

Type of Optics:

Circular

Physical & Mechanical Properties

|                         |                                           |
|-------------------------|-------------------------------------------|
| Black Anodized Aluminum | Construction:                             |
| 3.2                     | Max. Thickness of Compatible Optics (mm): |
| 52.0                    | Cell Diameter (mm):                       |

Threading & Mounting

|      |                                 |
|------|---------------------------------|
| 50.0 | Size of Compatible Optics (mm): |
| 5.0  | Cell Thickness (mm):            |

Regulatory Compliance

|                  |                             |
|------------------|-----------------------------|
| Exempt           | RoHS 2015:                  |
| View             | Certificate of Conformance: |
| Contains SVHC(s) | Reach 247:                  |

PRODUCT DETAILS

- Allows Stacking of 3 or 5 Filters
- Black Anodized Aluminum
- Posts and Post Holders Required for Mounting

Fixed/Multiple Filter Mounts are ideal for use with neutral density filters in stacking applications. Mounting cell holds filter with diameter "F" in place with a retainer ring. Mounting cell sits securely in filter holder. Fixed/Multiple Filter Mounts can also hold unmounted filters with diameter "A". A filter holder and filter cell are required for a complete stacking system, such as the one illustrated in the product image. These mounts are constructed of black anodized aluminum and are optimal for mounting 3 or 5 circular optics.


Posts and Post Holders are required for mounting to a breadboard.

TECHNICAL INFORMATION


| Stock No. | A    | B    | C    | D   | No. of Slots | No. of Cell Slots |
|-----------|------|------|------|-----|--------------|-------------------|
| #55-006   | 30mm | 50mm | 34mm | 5mm | 4            | 3                 |
| #55-007   | 50mm | 70mm | 44mm | 5mm | 5            | 5                 |

| Stock No. | F      | G      | H    |
|-----------|--------|--------|------|
| #56-759   | 12.7mm | 10.2mm | 30mm |
| #55-008   | 25mm   | 22.5mm | 30mm |
| #56-760   | 25.4mm | 22.9mm | 30mm |
| #55-009   | 50mm   | 47mm   | 52mm |

Multiple Filter Holder



Mounting Cell



Units: mm

