

Coherent® LabMax Touch Pro Power and Energy Meter 2256259

See More by [Coherent®](#)



Stock **#23-661** 2 In Stock

-

1

+

S\$3,549^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	S\$3,549.00 each
Need More?	Request Quote

Product Downloads

General	
2256259	Model Number:
Power and Energy	Type:
±1	Display Accuracy (%):
±1.0	Calibration Uncertainty (%):

Note: Meter supplied with Ac power adapter, power cord, USBcable, 2.5mm stereo AUX to DB9RS-232 cable, 3.5mm AUX to BNC Trigger-incable, Multi-Outputcable(analogout, triggerout, flagout), and certificate of calibration. Cat5 Ethernet cable and HDML cable are customer supplied. Coherent® Thermopile Power Sensors, Position Sensing Thermopile Power Sensors, Laser Energy Sensors, or High Sensitivity Sensors Sold Separately	
Physical & Mechanical Properties	
238.00	Length (mm):
238 x 162 x 51 mm	Dimensions (mm):
162.00	Width (mm):
1.19	Weight (kg):
51	Depth (mm):
Optical Properties	
±0.04% (25% to full scale), ±0.26% (5% to 25% of full scale), ±1% (min to 5% of full scale)	Resolution:
Electrical	
0 to 1, 2, or 4 VDC (selectable)	Analog Output:
10	Power Sampling Rate (Hz):
Hardware & Interface Connectivity	
90 to 260 VAC, 50/60 Hz AC	Power Supply:
Ethernet, USB, RS-232, PC application	Computer Interface:
Environmental & Durability Factors	
+5 to +40	Operating Temperature (°C):
-20 to +70	Storage Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Coherent® [Thermopile Power Sensors](#), [Position Sensing Thermopile Sensors](#), [Laser Energy Sensors](#), or [High Sensitivity Sensors](#) Sold Separately
 - FieldMate Used to Measure Laser Power
 - FieldMaxII Used to Measure Laser Power and Energy
 - ISO 17025 Certified
- Coherent® Laser Power and Energy Meters are designed to accurately measure and help tune the power or energy of continuous wave and pulsed lasers. The FieldMate, which features an analog needle with a large LCD display, is compatible with thermopile or optical sensors and is an economical solution for measuring laser power when advanced data analysis is not necessary. The FieldMaxII utilizes a large, backlit LCD screen and features a USB interface for computer connectivity. Coherent® Laser Power and Energy Meters feature FieldMaxII-TO, which is compatible with thermopile or optical sensors, while the FieldMaxII-TOP is compatible with thermopile, optical, or pyroelectric sensors. The LabMax is an all-in-one solution for measuring laser power or energy and is ideal for applications requiring advanced data analysis. The LabMax-TOP is compatible with thermopile, optical, or pyroelectric sensors. The LabMax Pro is the most advanced power and energy meter and is compatible with thermopile, optical, and pyroelectric sensors, as well as the PowerMaxPro high speed sensor technology. The LabMax Pro can provide advanced analysis up to 625kHz