

[See all 105 Products in Family](#)

# IDS U3-36P0XCP-M-GL, USB 3.0, 1/1.8" Monochrome Camera

See More by [IDS Imaging Development Systems](#)



IDS Imaging uEye+ USB3 Cameras



Stock #78-275 **5 In Stock**

⊖ 1 ⊕ **\$525<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1+	<b>\$525.00</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads

Monochrome	<b>Spectrum:</b>
------------	------------------

**General**

Monochrome Camera	<b>Type:</b>
U3-36P0XCP-M-GL	<b>Model Number:</b>
	<b>Manufacturer:</b>

uEye+ XCP **Camera Series:**

## Physical & Mechanical Properties

**Dimensions (mm):**  
29 x 29 x 17 (excludes connectors and lens mount)

**Weight (g):**  
60

**Housing:**  
Full

## Sensor

**Image Buffer:**  
Not Specified

**Sensor Format:**  
1/1.8"

**Resolution (Megapixels):**  
19.80

**Frame Rate (fps):**  
15.00

**Pixels (H x V):**  
5,120 x 3,840

**Pixel Size, H x V (µm):**  
1.40 x 1.40

**Sensing Area, H x V (mm):**  
7.168 x 5.376

**Imaging Sensor:**  
ON Semi AR2020

**Type of Sensor:**  
Progressive Scan CMOS

**Shutter Type:**  
Rolling

**Pixel Depth:**  
10 bit

**Exposure Time:**  
0.035ms - 2000ms

**Dynamic Range (dB):**  
63.00

**Machine Vision Standard:**  
USB3 Vision

## Electrical

**Power Consumption (W):**  
0.5 - 1.1

## Hardware & Interface Connectivity

**Interface:**  
USB 3.0

**Connector:**  
USB 3.0 micro-B, screwable

**Power Supply:**  
Power over USB

**GPIO Connector Type:**  
8-pin connector

## Threading & Mounting

**Mount:**  
C-Mount

## Environmental & Durability Factors

**Operating Temperature (°C):**  
0 to +55

**Storage Temperature (°C):**  
-20 to +60

## Regulatory Compliance

**Certificate of Conformance:**  
[View](#)

## Product Details

- Standard (SE), Compact (CP), and Ultra Compact (XCP) Housing Options Available

- C-Mount with Large Format CMOS Sensors up to 1.1"
- Up to 20.44MP Resolution with Framerrates up to 396fps

IDS Imaging uEye CP/XCP/SE USB3 Cameras utilize [IDS Imaging's peak SDK platform](#) that supports GeniCam and USB3 Vision standards for easy software development and integration. The CP cameras are the industry standard size of 29 x 29 x 29mm and work for almost any application. The XCP cameras have an ultra-compact size of 29 x 29 x 17mm and are an excellent option for price-sensitive, single-camera applications. The SE cameras have a larger housing size of 34 x 44 x 47mm to allow for exceptional heat management and are ideal for noise and heat-sensitive applications. IDS Imaging uEye CP/XCP/SE USB3 Cameras are ideal for manufacturing, industrial, and automation applications.

---