

## Lab Starter Kit, Metric Mounting



Lab Starter Kit (Not all products shown)

Stock **#37-090** [CONTACT US](#)

⊖ 1 ⊕ **S\$13,986<sup>00</sup>**

**ADD TO CART**

### Volume Pricing

Qty 1+	<b>S\$13,986.00</b> each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

**Contents of Kit:**

See Technical Information tab for a detailed list of items included in the kit

### Regulatory Compliance

Certificate of Conformance:

[View](#)

## Product Details

- Ideal Starting Point for New Labs
- 255 Individual Parts Included
- Optics, Optomechanics, Cleaning, Tools, and More
- English and Metric Based Mounting Versions Available

Lab Starter Kits are ideal for stocking a brand new lab. They feature essential products useful for any lab, from optics to detectors to cleaning and tools. Included in the kits are a range of lenses, filters, and prisms suited primarily for the visible spectrum. Lab Starter Kits also come with two light sources, a white LED, and a 640nm Coherent High Performance Stingray Laser Diode module. English and Metric mounting versions are available, with optomechanics and tools compatible with the included optics.

## Technical Information

	Description	Stock No.	Quantity
Optics	Optical Component Kit	#55-486	1
	25mm Simple Lens Kit	#48-613	1
	25mm Achromat Kit MgF <sub>2</sub>	#52-306	1
	VS, 25nm, 25mm Dia. Filter Kit	#88-300	1
	25mm Dia., Absorptive ND Kit	#63-469	1
	25mm Dia., VS Colored Glass Longpass Kit	#47-399	1
Mounting	C-Mount Extension Tube Kit	#54-668	1
	C-Mount Components Kit	#55-487	1
	70mm English Linear Translation Stage	#66-428	2
	70mm Verticle Stage (0.4" Travel)	#66-503	1
	25.4mm Optics Mount	#64-561	4
	25.4mm C-Mount Optics Holder	#56-354	2
	1/4-20 English Post Kit	#68-230	1
	1/4-20 English Post Holder Kit	#68-233	1
	2" x 3" Sliding Baseplate	#03-655	5
	Pivot Base	#53-355	5
	Dove Rail 12"	#54-401	1
	Dove Rail Carrier	#55-339	1
	2' x 3' Baseplate	#03-680	1
	1" Circular Kinematic Mount	#58-851	4
	70mm Bar-Type Clamp	#03-669	1
	110mm Bar-Type Clamp	#03-666	1
	60mm Rectangular Optics Mount	#54-995	1
Fixed Filter Mount	#54-997	1	
Illumination	5mW StingRay 640nm Laser	#86-849	1
	StingRay Power Supply	#59-099	1
	StingRay Mounting Adapter	#86-879	1
	M-LED Illuminator	#89-740	1
	Semi-Rigid Light Guide	#54-210	1
	Light Guide Adapter	#66-908	1
Cleaning	Cleaning Kit	#62-535	1
Tools	Spanner Wrench	#11-130	1
	Optical Component Case with Drawers	#59-815	1
	English Cap Screw Kit	#56-383	1
	Metric Cap Screw Kit	#56-384	1
	M6 Male to 1/4-20 Female Adapter	#53-927	5
	1/4-20 Male to M6 Female Adapter	#53-928	5
	Metric Ball Point Hex Driver Set	#88-155	1
	English Ball Point Hex Driver Set	#34-552	1
	Tweezers Kit	#86-719	1
Screwdriver Kit	#86-721	1	

	Description	Stock No.	Quantity
Optics	Optical Component Kit	#55-486	1
	25mm Simple Lens Kit	#48-613	1
	25mm Achromat Kit MgF <sub>2</sub>	#52-306	1
	VS, 25nm, 25mm Dia. Filter Kit	#88-300	1

	25mm Dia., Absorptive ND Kit	#63-469	1	
	25mm Dia., VS Colored Glass Longpass Kit	#47-399	1	
Mounting	C-Mount Extension Tube Kit	#54-668	1	
	C-Mount Components Kit	#55-487	1	
	70mm, Center Drive, Standard Top, Metric Extended Micrometer	#66-434	2	
	70mm, Metric Micrometer Z-Stage	#66-505	1	
	25.4mm Optics Mount	#64-561	4	
	25.4mm C-Mount Optics Holder	#56-354	2	
	Metric Post Kit, M6 Stud	#68-232	1	
	Metric Post Holder Kit	#68-234	1	
	85 x 50mm English Base Plate	#58-998	5	
	Pivot Base	#53-355	5	
	12" Dovetail Optical Rail	#54-928	1	
	Dove Rail Carrier	#54-931	1	
	900mm x 600mm, Breadboard	#87-214	1	
	1" Circular Kinematic Mount	#58-851	4	
	70mm Bar-Type Clamp	#03-669	1	
	110mm Bar-Type Clamp	#03-666	1	
	60mm Rectangular Optics Mount	#54-995	1	
	Fixed Filter Mount	#54-997	1	
	Illumination	5mW StingRay 640nm Laser	#86-849	1
		StingRay Power Supply	#59-099	1
StingRay Mounting Adapter		#86-879	1	
M-LED Illuminator		#89-740	1	
Semi-Rigid Light Guide		#54-210	1	
Light Guide Adapter		#66-908	1	
Cleaning	Cleaning Kit	#62-535	1	
Tools	Spanner Wrench	#11-130	1	
	Optical Component Case with Drawers	#59-815	1	
	English Cap Screw Kit	#56-383	1	
	Metric Cap Screw Kit	#56-384	1	
	M6 Male to 1/4-20 Female Adapter	#53-927	5	
	1/4-20 Male to M6 Female Adapter	#53-928	5	
	Metric Ball Point Hex Driver Set	#88-155	1	
	English Ball Point Hex Driver Set	#34-552	1	
	Tweezers Kit	#86-719	1	
	Screwdriver Kit	#86-721	1	