

Ring Light 56mm, 0° Divergence



Stock **#20-180** 1 In Stock

-

1

+

S\$1,001⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$1,001.00 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

SPECIFICATIONS

General

10000

Operating Lifetime (hours):

378	Number of LEDs:
Contents of Kit: Ring light, mounting plate, retrofit clamp for smaller ID mounting options, diffuser, polarizer, extension cable	
LED Illuminator	Type of Illumination:
Note: Compatible with EO Lenses: 33-101, 33-115	
Visionlux Technology	Manufacturer:
Geometry: Ring Light	
Physical & Mechanical Properties	
56.0	Inner Diameter (mm):
131.8	Outer Diameter (mm):
545	Weight (g):
Optical Properties	
White	Color:
126, 163, 200	Working Distance (mm):
57600, 45000, 32900	Irradiance (W/cm²):
Hardware & Interface Connectivity	
Power Supply: Power Supply Required and Sold Separately: USA: #15-280 and #73-651 Europe: #73-651	
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- Designed for use with [TECHSPEC® CompactTL™ Telecentric Lenses](#)
- Built-in Cooling Fins for Consistent, High Intensity Performance
- Includes Easy to Integrate Polarizer and Diffuser

LED Ring Lights for Telecentric Lenses provide high intensity and uniform LED illumination with a divergence angle optimized for telecentric lens working distances. Designed to integrate directly with [TECHSPEC® CompactTL™ Telecentric Lenses](#), these ring lights attach without the need for additional custom mounting. Featuring a sturdy metal casing and built in cooling fans, LED Ring Lights for Telecentric Lenses allow for continuous operation over extended periods of time. A mounting plate, clamp, diffuser, polarizer, and extension cable are all included in purchase of a LED Ring Light for Telecentric Lenses.

Note: Power Supply [#73-651](#) is required (sold separately).

TECHNICAL INFORMATION

RING LIGHT KIT FOR TECHSPEC® COMPACTTL™ AND TECHSPEC® SILVERTL™ TELECENTRIC LENSES (#20-186)		
QTY.	Stock No.	Description
1	#20-177	18mm Inner Diameter, 15 Deg. Divergence
1	#20-178	22mm Inner Diameter, 15 Deg. Divergence
1	#20-179	29.5mm Inner Diameter, 15 Deg. Divergence
1	#20-180	31mm Inner Diameter, 0 Deg. Divergence
1	#20-181	32mm Inner Diameter, 15 Deg. Divergence
1	#20-182	36mm Inner Diameter, 15 Deg. Divergence
1	#20-184	40mm Inner Diameter, 15 Deg. Divergence
1	#20-187	Spotlight
7		Ring Light Diffusers
7		Ring Light Polarizers
12		Compatibility Clamps
1		M12 Extension Cable
1		Controller
1		Power Cord UK
1		Power Cord US
1		Suitcase