


White 225mm Compact Light w/ Dual OverDrive™



Stock #23-949 **1 In Stock**



S\$1,953^{.00}

ADD TO CART

225mm Compact Light



Volume Pricing	
Qty 1+	S\$1,953.00 each
Need More?	Request Quote

Product Downloads	
STEP:step	IGES:igs
Spec Sheets:pdf	
eDrawing:eprt	
EO Spec Sheet	Download All

General

Model Number:	JWL225-DO-WHI	Type of Illumination:	LED Illuminator
Manufacturer:	Smart Vision Lights LLC	Geometry:	Ring Light
Illumination Mode:	Constant or Strobed		

Physical & Mechanical Properties

Dimensions (mm):	230 W x 142 H x 45D (60.40 D Including Connector)	Weight (g):	1496.85
Active Area (mm):	144.50W x 56.5H		

Optical Properties

Color:	White	Working Distance (mm):	500 - 2,000
---------------	-------	-------------------------------	-------------

Electrical

Strobe Duration (µs):	10 - 7,000		
------------------------------	------------	--	--

Hardware & Interface Connectivity

Connector:	5-pin M12 connector	Input Voltage (V):	24 VDC ± 5%
-------------------	---------------------	---------------------------	-------------

Threading & Mounting

Mount:	T-Slot for M6 Nut		
---------------	-------------------	--	--

Environmental & Durability Factors

Operating Temperature (°C):	-10° to +40°	Environmental Rating:	IP65
------------------------------------	--------------	------------------------------	------

Regulatory Compliance

Product Details

- Utilize Dual OverDrive™ Technology for 10x Standard Light Output
- Offer Illumination Coverage over a Larger Field of View
- Direct Connect and Control via Camera's Trigger Output
- Ideal for High Speed Logistics Applications

Smart Vision Lights High Output Ring Lights are IP65-rated brightfield lights featuring a working distance of 500-mm to 2000-mm that can be directly connected to a camera for control via the trigger output. Built-in Dual OverDrive™ technology, which delivers up to 6 times the continuous power with a low-latency response and fast strobe durations down to 10ms. These lights feature a batwing design that illuminates a larger area than built-in lighting systems and produces a greater light output making them ideal to use alongside polarizers, diffusers, and other optical elements that reduce light output. Smart Vision Lights Illumination products offer an industry-leading 10-year limited warranty.

Accessories

Note: Compatible accessories for individual stock numbers may vary. If unsure about which accessories work with your products, please contact us [here](#).

	Title	Compare	Stock Number	Price	Buy
MORE+	Smart Vision Lights 5 Pin 5 Meter Cable (16.4 feet)		#23-951	S\$84.70 Request Quote	CONTACT US 1
MORE+	Smart Vision Lights 5 Pin 10 Meter Cable (32.8 feet)		#23-952	S\$112.00 Request Quote	2 In Stock 1
MORE+	Smart Vision Lights 5 Pin 15 Meter Cable (49.2 feet)		#23-953	S\$133.00 Request Quote	CONTACT US 1
MORE+	Smart Vision Lights Mounting Bracket		#23-954	S\$98.00 Request Quote	2 In Stock 1
MORE+	Smart Vision Lights Controller		#89-709 NEW	S\$2,037.00 Request Quote	CONTACT US 1

Related Products



Smart Vision Lights Compact Ring Lights



Edmund Optics E Series Fixed Focal Length Lenses



Allied Vision Mako Power over Ethernet (PoE) Cameras



IDS Imaging uEye+ FA IP65/67 PoE Cameras