

# White 225mm Compact Light w/ Multi-Drive™



225mm Compact Light



Stock **#23-946** [CONTACT US](#)

-

1

+

S\$1,953<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | S\$1,953.00 each              |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General                 |                       |
|-------------------------|-----------------------|
| JWL225-MD-WHI           | Model Number:         |
| LED Illuminator         | Type of Illumination: |
| Smart Vision Lights LLC | Manufacturer:         |
| Ring Light              | Geometry:             |

|                                                   |  |
|---------------------------------------------------|--|
| Illumination Mode:                                |  |
| Constant or Strobed                               |  |
| Physical & Mechanical Properties                  |  |
| Dimensions (mm):                                  |  |
| 230 W x 142 H x 45D (60.40 D Including Connector) |  |
| Weight (g):                                       |  |
| 1496.85                                           |  |
| Active Area (mm):                                 |  |
| 144.50W x 56.5H                                   |  |
| Optical Properties                                |  |
| Color:                                            |  |
| White                                             |  |
| Working Distance (mm):                            |  |
| 500 - 2,000                                       |  |
| Electrical                                        |  |
| Strobe Duration (µs):                             |  |
| 30 - ∞                                            |  |
| Hardware & Interface Connectivity                 |  |
| Connector:                                        |  |
| 5-pin M12 connector                               |  |
| Input Voltage (V):                                |  |
| 24 VDC ± 5%                                       |  |
| Threading & Mounting                              |  |
| Mount:                                            |  |
| T-Slot for M6 Nut                                 |  |
| Environmental & Durability Factors                |  |
| Operating Temperature (°C):                       |  |
| -10° to +40°                                      |  |
| Environmental Rating:                             |  |
| IP65                                              |  |
| Regulatory Compliance                             |  |
| Certificate of Conformance:                       |  |
| <a href="#">View</a>                              |  |

## Product Details

- Direct Connect and Control via Camera's Trigger Output
- Built-In Multi-Drive™ Technology
- T-Slots for Mounting

Smart Vision Lights Compact Ring Lights are IP65-rated brightfield lights featuring a working distance of 500-mm to 2000-mm that can be directly connected to a camera for control via the trigger output. Built-in Multi-Drive™ technology, which offers both continuous operation and OverDrive™ mode, delivers up to 6 times the continuous power with a low-latency response and fast strobe durations down to 10mS. These lights feature a batwing design that illuminates a larger area than built-in lighting systems and produces a greater light output making them ideal to use alongside polarizers, diffusers, and other optical elements that reduce light output. Smart Visions Lights Illumination products offer an industry-leading 10-year limited warranty.