



TECHSPEC® Achromatic Lenses

TECHSPEC® ACHROMATIC LENSES

Edmund Optics Inc.

USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy



47663 TUE DEC 16 2008 UNITS ARE μm .

FIELD : 12.033

RMS RADIUS : 33.667

SCALE BAR : 100

REFERENCE : CHIEF RAY



EDMUND OPTICS
[HTTP://WWW.EDMONDOPTICS.COM](http://WWW.EDMONDOPTICS.COM)

EDMUND OPTICS
[HTTP://WWW.EDMONDOPTICS.COM](http://WWW.EDMONDOPTICS.COM)

CHROMATIC FOCAL SHIFT

47663 TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 75.7268 μm
DIFFRACTION LIMITED RANGE: 13.200 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
[HTTP://WWW.EDMONDOPTICS.COM](http://WWW.EDMONDOPTICS.COM)



TRANSVERSE RAY FAN PLOT

47663 TUE DEC 16 2008
MAXIMUM SCALE: ± 100.000 μm .
0.486 0.588 0.656

SURFACE: IMAGE

EDMUND OPTICS
[HTTP://WWW.EDMONDOPTICS.COM](http://WWW.EDMONDOPTICS.COM)

POLYCHROMATIC DIFFRACTION MTF

47663 TUE DEC 16 2008
DATA FOR 0.4250 TO 0.6750 μm .
SURFACE: IMAGE

EDMUND OPTICS
[HTTP://WWW.EDMONDOPTICS.COM](http://WWW.EDMONDOPTICS.COM)