


NOTES:

1. SUBSTRATE
2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN 5 arcsec
3. COATING (APPLY ACROSS COATING APERTURE)  
ENVIRONMENTAL DURABILITY:  
PHYSICAL DURABILITY:  
PERFORMANCE SPECIFICATIONS:  
T(avg): >85% FROM 420 - 1600nm FOR RANDOM POLARIZATION @ 45° AOI  
T(abs): >80% FROM 420 - 1600nm FOR ALL POLARIZATIONS @ 45° AOI  
R(avg): >97% FROM 350 - 375nm FOR RANDOM POLARIZATION @ 45° AOI  
R(abs): >95% FROM 350 - 375nm FOR ALL POLARIZATIONS @ 45° AOI  
T(abs): = 50% 400nm @ 45° AOI

S1: HARD COATED  
S2: SINGLE LAYER MgF2



4. FINE GRIND SURFACE

5. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS  
APPLY ACROSS CLEAR APERTURE
6. TRANSMITTED WAVEFRONT DISTORTION RMS@ 632.8nm  $\leq \frac{1}{4} \lambda$
7. ROHS COMPLIANT





LONGPASS FILTER

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	 <b>Edmund Optics®</b>			
SHAPE	PLANO	PLANO		TITLE	12.5 x 17.6mm, 900nm DICHROIC LONGPASS FILTER	
SURFACE QUALITY	60-40	60-40		DWG NO	69875	SHEET 1 OF 1
CLEAR APERTURE	11.0 x 16.0	11.0 x 16.0				
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm		