



NOTES:

1. SUBSTRATE
2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN 10 ARCSEC
3. COATING (APPLY ACROSS CLEAR APERTURE)  
PHYSICAL DURABILITY: MIL-C-48497A  
ENVIRONMENTAL DURABILITY: MIL-STD-810F  
Tavg ≥93% @ 538.9 - 1200nm
4. FINE GROUND SURFACE
5. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY  
ACROSS CLEAR APERTURE
6. TRANSMITTED WAVEFRONT DISTORTION RMS @ <λ/4 @ 633nm
7. RoHS COMPLIANT

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2	<div><div><div><div><div></div></div></div><div><div></div></div></div><div>THIRD ANGLE PROJECTION</div></div> <div><div>Edmund Optics®</div><div>TITLE</div><div>Ø25mm, 537.3nm, RAMAN EDGE FILTER</div></div>			
SHAPE	PLANO	PLANO				
SURFACE QUALITY	60-40	60-40				
CLEAR APERTURE	>80%	>80%				
REJECTION WAVELENGTH	430 - 532	430 - 532				
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED				
			ALL DIMS IN	mm	DWG NO	86242
						SHEET 1 OF 1