



TECHSPEC® ACHROMATIC LENSES



TECHSPEC® ACHROMATIC LENSES



Surface: IMA

Spot Diagram		Edmund Optics HTTP://WWW.EDMUNDOPTICS.COM
33922 4/24/2017 Units are μm. Airy Radius: 1.465 μm. Legend items refer to Wavelengths Field : 1 mm RMS radius : 119.796 GEO radius : 302.485 Scale bar : 1000 Reference : Chief Ray	33922.ZMX Configuration 1 of 1	

Edmund Optics HTTP://WWW.EDMUNDOPTICS.COM	Chromatic Focal Shift
33922 4/24/2017 Maximum Focal Shift Range: 339.9297 μm Diffraction Limited Range: 9.815 μm Pupil Zone: 0.0000	33922.ZMX Configuration 1 of 1



Transverse Ray Fan Plot				Edmund Optics HTTP://WWW.EDMUNDOPTICS.COM
33922 4/24/2017 Maximum Scale: ± 500.000 μm. 0.486 0.588 0.656				33922.ZMX Configuration 1 of 1

Polychromatic Diffraction MTF				Edmund Optics HTTP://WWW.EDMUNDOPTICS.COM
33922 4/24/2017 Data for 0.4861 to 0.6563 μm. Surface: Image				33922.ZMX Configuration 1 of 1



Edmund
optics | worldwide

www.edmundoptics.com