



NOTES:

1. SUBSTRATE MATERIAL:  
N-BK7
2. COATING (APPLY ACROSS CLEAR APERTURE)
- S1 & S2: VIS 0°
- R(avg) ≤0.4% @ 425 - 675nm



3. FINE GROUND SURFACE

4. POWER, IRREGULARITY, AND SURFACE QUALITY  
SPECIFICAIONS APPLY ACROSS CLEAR APERTURE
5. RoHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

|                  |                     |                     |  |    |        |  |                 |     |       |
|------------------|---------------------|---------------------|--|----|--------|--|-----------------|-----|-------|
| REV. A           | S1                  | S2                  |  Edmund Optics® |    |        |  |                 |     |       |
| SHAPE            | CONVEX              | PLANO               |  |    |        |  |                 | EFL | -50   |
| RADIUS           | 25.84               | ∞                   |  |    |        |  |                 | BFL | -52.6 |
| SURFACE QUALITY  | 60-40               | 60-40               |                 |    | TITLE  | 25mm H X 50mm L X -50mm FL VIS 0°<br>COATED, CYLINDER LENS |                 |     |       |
| CLEAR APERTURE   | 24.00 X 49.00       | 24.00 X 49.00       |  |    |        |  |                 |     |       |
| COATING APERTURE | 24.00 X 49.00       | 24.00 X 49.00       |  |    |        |  |                 |     |       |
| BEVEL            | PROTECTED AS NEEDED | PROTECTED AS NEEDED | ALL DIMS IN  | mm | DWG NO | 69807  | SHEET<br>1 OF 1 |     |       |