

1. SUBSTRATE:
N-BK7


3. COATING (APPLY ACROSS CLEAR APERTURE)

S1: 40% R \pm 5% @ 900nm
60% T \pm 5% @ 900nm

S2: AR $R(\text{avg}) \leq 1\%$, $R(\text{abs}) \leq 2\%$ @ 700 - 1100nm

4. CUT WITH 0.25mm MAXIMUM EDGE CHIP



5. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



	S1	S2	 Edmund Optics®				
SHAPE	PLANO	PLANO	<div>THIRD ANGLE PROJECTION</div> 		TITLE	25 x 38mm 40R/60T, NIR Plate Beamsplitter	
ANGLE OF INCIDENCE	45°	45°					
SURFACE QUALITY	60 - 40	60 - 40					
SURFACE FLATNESS	1λ PER 25mm	1λ PER 25mm	ALL DIMS IN	mm	DWG NO	68390	SHEET 31 OF 49