


NOTES:

- 1. SUBSTRATE: LIBA2000+
- 2. COATING:
S1 & S2: UNCOATED
- 3. FOCAL LENGTH TOLERANCE: ±7%
- 4. CENTERING: 25 ARCMIN
- 5. RoHS: COMPLIANT
- 6. ASPHERIC SURFACE DESCRIBED BY THE FOLLOWING EQUATION AND COEFFICIENTS SHOWN IN TABLE BELOW

$$Z_{ASPH}(Y) = \frac{(\frac{1}{RADIUS}) * Y^2}{1 + \sqrt{1 - (1 + k) * (\frac{1}{RADIUS})^2 * Y^2}} + D * Y^2 + E * Y^4 + F * Y^6 + G * Y^8 + H * Y^{10} + J * Y^{12} + L * Y^{14}$$



FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING



COEFFICIENT TABLE	
COEFFICIENT	S1
SEMI-DIAMETER	15.000000E+00
(1/RADIUS)	7.818608E-02
k	-0.900000E+00
D	0.000000E+00
E	0.000030E+00
F	-1.000000E-06
G	5.100000E-09
H	-1.000000E-11
J	0.000000E+00
L	0.000000E+00

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	CONVEX	CONVEX
SURFACE QUALITY	As Molded	As Molded
CLEAR APERTURE	Ø24.00	Ø24.00
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

EFL: 17.5mm		 Edmund Optics®	
BFL: 10.37mm			
		TITLE	30mm DIA. X 17.5mm FL, UNCOATED MOLDED ASPHERIC CONDENSER LENS
ALL DIMS IN	mm	DWG NO	88291
			SHEET 1 OF 1