


NOTES:

1. SUBSTRATE MATERIAL:  
N-SF5
2. COATING (APPLY ACROSS CLEAR APERTURE)  
  
S1: ENHANCED ALUMINUM  
R(avg) >95% @ 450 - 650nm  
  
S2: NONE
3. POWER, IRREGULARITY, SURFACE QUALITY, AND COATING  
SPECIFICATIONS APPLY ACROSS CLEAR APERTURE
4.

FINE GROUND SURFACE
5. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2	<div><div>THIRD ANGLE PROJECTION</div><div></div></div>				<div><div></div><div>Edmund Optics®</div></div>		
SHAPE	CONVEX	PLANO							
RADIUS	15.5	INFINITY							
EFFECTIVE FOCAL LENGTH	-7.75mm	N/A							
FOCAL LENGTH TOLERANCE	±2%	N/A							
SURFACE QUALITY	60-40	COMMERCIAL POLISH	ALL DIMS IN	mm	TITLE	Ø12mm, -7.75mm FL ENHANCED ALUMINUM, CONVEX SPHERICAL MIRROR			
CLEAR APERTURE	90%	N/A							
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	DWG NO		64056		SHEET 1 OF 1		