

NOTES:


1. SUBSTRATE MATERIAL:  
N-BK7
2. COATING (APPLY ACROSS CLEAR APERTURE)

S1 & S2:  
LASER V-COAT

R(abs) <0.25% @ 1064nm



3. FINE GROUND SURFACE

4. POWER, IRREGULARITY, AND SURFACE QUALITY  
SPECIFICAIONS APPLY ACROSS CLEAR APERTURE
5. RoHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	<div>EFL50±3%</div> <div>BFL(48.75)</div> <div> Edmund Optics®</div>					
SHAPE	CONVEX	PLANO						
RADIUS	25.93	∞						
SURFACE QUALITY	60-40	60-40	<div>THIRD ANGLE PROJECTION</div> <div></div>		TITLE	12.5mm DIA X 50.0mm FL 1064nm V-COAT, CYLINDER LENS		
CLEAR APERTURE	Ø 11.50	Ø 11.50						
COATING APERTURE	Ø 11.50	Ø 11.50						
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED	ALL DIMS IN	mm	DWG NO	33232	SHEET 1 OF 1	