


NOTES:

1. SUBSTRATE: L-BAL35
2. COATING (APPLY ACROSS CLEAR APERTURE)
S1: R(avg) ≤1.5% @ 600 - 1050nm
S2: R(avg) ≤1.5% @ 600 - 1050nm
3. EDGES: FINE GROUND
4. CENTERING: <3-5 ARCMIN
5. ASPHERE FIGURE ERROR: 0.75 μm RMS

△6. ASPHERIC SURFACE DESCRIBED BY (REF. COEFFICIENT TABLE)

$$Z_{ASPH}(Y) = \frac{(1/RADIUS)^*Y^2}{1 + \sqrt{1 - (1+k)*(1/RADIUS)^2*Y^2}} + D*Y^2 + E*Y^4 + F*Y^6 + G*Y^8 + H*Y^{10} + J*Y^{12} + L*Y^{14}$$



COEFFICIENT TABLE △7

COEFFICIENT	S1
SEMI-DIAMETER	7.500000E+00
(1/RADIUS)	0.090531E+00
k	-1.832442E+00
D	0.000000E+00
E	1.166845E-04
F	-2.157671E-07
G	9.596239E-10
H	-2.541401E-12
J	0.000000E+00
L	0.000000E+00

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL @ 587.6μm	18.75	 Edmund Optics®		
SHAPE	CONVEX	PLANO	BFL @ 587.6μm	15.92			
RADIUS	11.046	INFINITY			TITLE	15mm DIA., 0.40 NUMERICAL APERTURE NIR COATED, ASPHERIC LENS	
SURFACE QUALITY	60-40	60-40					
CLEAR APERTURE	90%	90%	ALL DIMS IN mm		DWG NO	49111	
BEVEL MAX	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED					
							SHEET 1 OF 1