





NOTES:

- 1.  ARROW INDICATOR SHOWS BEAM PATH
- 2. RoHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

CLEAR APERTURE (mm)	4.7
DAMAGE THRESHOLD (CW)	41 W, 4 kW/cm ² @ DWL
DESIGN WAVELENGTH DWL (nm)	780
MIN ISOLATION @ DWL (dB)	38
OPERATING TEMPERATURE	+15 C to 40 C
TRANSMISSION (%)	92 (typical)
TYPICAL ISOLATION @ DWL (dB)	43



ALL DIMS IN mm

TITLE	780nm Single Stage Free-Space Optical Isolator		
DWG NO	35973	SHEET	1 OF 1