

FOCAL LENGTH (EFL): 200 ± 2
 BACK FOCAL LENGTH (BFL): $197,36$

1 AR COATING:

$\frac{1}{4}$ WAVE MgF_2 @ 550nm
 $R(\text{AVG}) < 1,75\%$ FROM $400-700\text{nm}$ (N-BK7)

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$207,93 \pm 0,208 \text{ CX}$	GLASS N-K5 523/595	R	$207,93 \pm 0,208 \text{ CX}$
Øe	39		Øe	39
3/	$3 (0,5) \lambda = 632,8 \text{ nm}$		3/	$3 (0,5) \lambda = 632,8 \text{ nm}$
4/	-		4/	$1,91'$
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED


ROHS: COMPLIANT
 SCALE: NONE $\lambda = 587,6\text{nm}$

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE 40mm Dia, x 200mm FL, MgF2 Coated, DCX N-K5 Lens

DWG NO 32911

SHEET SIZE A4 SHEET 1 OF 1