
NOTES:


- 1. SUBSTRATE: ZnSe
- 2. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN < 3 ARCMIN
- 3. COATING (APPLY ACROSS COATING APERTURE)

\$1& \$2: HIGH- EFFICIENCY BROADBAND (BBAR) $R(AVG) \le 0.5\%$ FROM 8 - $12\mu m$



5. RoHS: COMPLIANT





FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2		
SHAPE	PLANO	PLANO		
SURFACE QUALITY	40-20	40-20		
SURFACE FLATNESS @ 10.6µm	λ/20	λ/20	THIRD AN	
CLEAR APERTURE	Ø22.50	Ø22.50		
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIM	

THIRD ANGLE PROJECTION	$\phi \triangleleft$	TITLE
ALL DIMS IN	mm	DWG NO

Edmund Optics®
 25mm DIA x 5mm THICK 8 - 12µm COATED

1 OF 1

GLE_ ION	$\bigoplus \Box$	TITLE	25mm DIA x 5mm THICK 8 - 12µm COAT ZnSe WINDOW	ED
INI 2	mm	DWG NO	00.401	SHEET

39421