


NOTES:  
1. RoHS: EXEMPT


**FOR INFORMATION ONLY:**  
**DO NOT MANUFACTURE**  
**PARTS TO THIS DRAWING**



	VALUE
WEIGHT (lbs)	0.46
WARM-UP TIME	10
RMS NOISE	30 Hz - 10 MHz: 0.1%
OPERATING TEMPERTURE (°C)	-40 to +70
OPERATING HUMIDITY	0 TO 100%, NON-CONDENSING
MODE PURITY (TEM00)	>95%
MINIMUM OUTPUT POWER, TEM00 (mW)	0.8
MAXIMUM DRIFT	MEAN POWER OVER 8 HRS: ±2.5
LONGITUDINAL MODE SPACING, NOMINAL (MHz)	1090
LASER CLASS - CDRH	IIIa
COLOR	RED
POINTING STABILITY AFTER WARM UP (mrad/°C)	N/A
POINTING STABILITY (mrad/°C)	N/A
OUTPUT POWER (mW)	0.8
BEAM DIAMETER (mm)	0.48
BEAM DIVERGENCE (mrad)	1.70 ± 3
POLARIZATION	500:1
STATIC ALIGNMENT	CENTERED TO OUTER CYLINDER: ±0.01" PARALLEL TO OUTER CYLINDER: ±1.0 MRAD

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**EO**® **Edmund Optics**®

THIRD ANGLE PROJECTION 		TITLE	Model 1107P, 0.8mW Linear Polarization, Lumentum HeNe Laser	
ALL DIMS IN	in	DWG NO	62717	SHEET 1 OF 1