



FOCAL LENGTH (EFL): 50 ±0,5
 BACK FOCAL LENGTH (BFL): 49

1 AR COATING: NONE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	51,16±0,051 CX	GLASS N-BK7 517/642	R	51,16±0,051 CX
Øe	14		Øe	14
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	1,93'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED		FIRST ANGLE PROJECTION				
ROHS: COMPLIANT	SCALE: NONE λ = 587,6nm					
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			TITLE	15mm Dia, x 50mm FL Uncoated, Double-Convex Lens		
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING			ALL DIMS IN: mm	DWG NO	32938	SHEET SIZE A4
INDICATIONS IN ACCORDANCE WITH ISO 10110						