





FOCAL LENGTH (EFL): 18 ±0,18
 BACK FOCAL LENGTH (BFL): 15,61

1 AR COATING: 980nm V-COAT
 R(ABS) < 0,25% @ 980nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	12,11±0,012 CX	GLASS N-SF5 673/322	R	∞ PL
Øe	14		Øe	14
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	1,49'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION		 Edmund Optics®			
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm			TITLE 15,0mm Diameter x 18,0mm FL, 980nm V-Coat , PCX Lens			
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY								DWG NO 87614
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING					ALL DIMS IN: mm		SHEET SIZE A4	
INDICATIONS IN ACCORDANCE WITH ISO 10110							SHEET 1 OF 1	