





FOCAL LENGTH (EFL): 75 ±0,75
BACK FOCAL LENGTH (BFL): 72,94

1 AR COATING: NONE

LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R	34,385±0,034 CX		GLASS FUSED SILICA 458/678	R	∞ PL	
Øe	14			Øe	14	
3/	3 (0,5) λ=632,8 nm			3/	3 (0,5) λ=632,8 nm	
4/	-			4/	2,18'	
5/	40 - 20 (MIL-PRF-13830B)			5/	40 - 20 (MIL-PRF-13830B)	
6/	-			6/	-	
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®		
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE 15mm Dia, x 75mm FL Uncoated, UV Plano-Convex Lens		
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				DWG NO 84281		
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN: mm	SHEET SIZE A4		SHEET 1 OF 1