



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

NOTES:


1. SUBSTRATE: ISUZU ISK157  
DENSITY: 2.60g/cm³  
REFLECTION FACTOR: 0.92  
KNOOP HARDNESS: 481kg/mm²  
REFRACTIVE INDEX: 1.518nm
2. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN 3 ARCMIN




SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

|                 |                      |
|-----------------|----------------------|
|                 | S1                   |
| SHAPE           | PLANO                |
| FUNCTION        | HEAT ABSORBING       |
| SURFACE QUALITY | 60-40                |
| CLEAR APERTURE  | Ø11.25               |
| BEVEL MAX FACE  | PROTECTIVE AS NEEDED |

THIRD ANGLE  
PROJECTION



ALL DIMS INmm

 Edmund Optics®

TITLEISUZU ISK157, 12.5 Dia., HEAT ABSORBING  
COLORED GLASS FILTER

DWG NO15700

SHEET  
1 OF 1