



NOTES:

- SUBSTRATE: N-BK7
- COATING (APPLY ACROSS CLEAR APERTURE)
S1: NONE
S2: NONE
- EDGES: FINE GROUND
- CENTERING: <3 ARCMIN
- ASPHERE FIGURE ERROR: 0.25 µm RMS

6. BLACKENED SURFACE

7. ASPHERIC SURFACE DESCRIBED BY (REF. COEFFICIENT TABLE)

$$Z_{\text{ASPH}}(Y) = \frac{(1/\text{RADIUS}) * Y^2}{1 + \sqrt{1 - (1+k) * (1/\text{RADIUS})^2 * Y^2}} + D * Y^2 + E * Y^4 + F * Y^6 + G * Y^8 + H * Y^{10} + J * Y^{12} + L * Y^{14}$$




SECTION A-A

COEFFICIENT TABLE 6.

COEFFICIENT	S1
SEMI-DIAMETER	1.000000E+01
(1/RADIUS)	3.869969E-02
k	-8.004240E-01
D	0.000000E+00
E	1.643994E-06
F	5.887865E-10
G	0.000000E+00
H	0.000000E+00
J	0.000000E+00
L	0.000000E+00

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL @ 587.6nm	50.00	 Edmund Optics®		
SHAPE	CONVEX	PLANO	BFL @ 587.6nm	45.23			
RADIUS	25.840	INFINITY			TITLE	25mm DIA., 0.25 NUMERICAL APERTURE, UNCOATED, INKED, HIGH PRECISION ASPHERIC LENS	
SURFACE QUALITY	40-20	40-20					
CLEAR APERTURE	Ø24.00	Ø24.00					
BEVEL MAX	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	37431INK	SHEET 1 OF 1

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**