

1. SUBSTRATE:
SCHOTT KG5



2. COATING (APPLY ACROSS CLEAR APERTURE)

S1 & S2: NONE

3. FINE GRIND SURFACE

4. DENSITY (g/cm³) : 2.53
OPERATING TEMPERATURE (°C): 300 Maximum
REFLECTION FACTOR: 0.92


5. ROHS COMPLIANT



FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



	S1	S2	<div>THIRD ANGLE PROJECTION</div> 		<div>TITLE</div> <div>SCHOTT KG5, 25mm Dia., 1mm Thick, Colored Glass Heat Absorbing Shortpass Filter</div>						
SHAPE	PLANO	PLANO						<div>DWG NO</div> <div>19333</div>		<div>SHEET 1 OF 1</div>	
SURFACE QUALITY	60-40	60-40									
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED	ALL DIMS IN	mm							