NOTES:

1. SUBSTRATE: FLOAT GLASS


2. COATING (APPLY ACROSS CLEAR APERTURE)

\$1 & \$2: BBAR (425-700nm) R(AVG) ≤0.5% @ 425 - 700nm



3. FINE GRIND SURFACE

4. ROHS COMPLIANT



PARTS TO THIS DRAWING

DIMENSIONS ARE FOR REFERENCE ONLY

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE

SHEET 2 OF 4

	\$1	\$2
Shape	PLANO	PLANO
SURFACE QUALITY	80 - 50	80 - 50
CLEAR APERTURE	Ø 22.50	Ø 22.50
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

			Edmund Option	S®
THIRD ANGLE PROJECTION	\rightarrow	TITLE	25mm Dia. x 1mm High Efficiency Win	dow
ALL DIMS IN	mm	DWG NO	21325	SHEET 2 OF