



- NOTES:
- 1. SUBSTRATE: POLYMER FILM XP44-40
 - 2. OPERATING TEMPERATURE: -40 TO +80 °C
 - 3. WAVELENGTH RANGE: 400 - 700 nm
 - 4. EXTINCTION RATIO: 2000:1
 - 5. POLARIZATION EFFICIENCY (%): >99.95
 - 6. TRANSMISSION (%):
 - SINGLE: 44.2 ±1.5
 - PARALLEL: 38.6
 - CROSSED: <0.02
 - 7. ROHS COMPLIANT
 - 8. THE POLARISATION AXIS IS PARALLEL TO THE NOTCH ON THE POLARISER



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

 Edmund Optics®			
THIRD ANGLE PROJECTION 		TITLE	100 x 100mm High Transmission Linear Polarizing Film (XP44-40)
ALL DIMS IN	mm	DWG NO	19020
			SHEET 1 OF 1