## NOTES:

- 1. SUBSTRATE: SAPPHIRE (AL2O3)
- 2. SURFACE \$1 TO BE PARALLEL WITH SURFACE \$2 TO WITHIN ≤3.5 ARCMIN
- 3. ENVIRONMENTAL REQUIREMENTS:

S1 & S2: HIGH DURABILITY BBAR (2000-5000nm) ADHESION: PER MIL-M-13508C PARA 4.4.6 ABRASION: SEVERE PER MIL-C-675C PARA 4.5.10

HUMIDITY: PER MIL-C-675C PARA 4.5.8 SALT SOLUBILITY: PER MIL-C-675C PARA 4.5.7 SALT SPRAY: PER MIL-C-675C PARA 4.5.9

TEMPERATURE CYCLE: PER MIL-M-13508C PARA 4.4.4





S1 & S2:

R(AVG) <1.5% @ 2000 - 5000nm R(ABS) <2.0% @ 2000 - 5000nm



6. ROHS COMPLIANT





## FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2	
SHAPE	PLANO	PLANO	
SURFACE QUALITY	80-50	80-50	
CLEAR APERTURE	Ø 18.00	Ø 18.00	
SURFACE FLATNESS	2λ (typical)	2λ (typical)	
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED	

				Edmund Optic	S®
	THIRD ANGLE PROJECTION		TITLE	20mm Dia., 0.5mm Thick, 2000-5000nm, High Durability AR Coated Sapphire Window	
D	ALL DIMS IN	mm	DWG NO	18470	SHEET 1 OF 1

