

## NOTES:


1. SUBSTRATE: VACUUM UV GRADE CaF2

- 2. SURFACE S2 TO BE PARALLEL WITH S1 TO < 1 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE) \$1 & \$2: R(ABS) ≤ 0.25% AT 880nm @ 0° AOI R(AVG) ≤ 1.25% FROM 400-870nm @ 0° AOI R(AVG) ≤ 1.25% FROM 890-1000nm @ 0° AOI

4. FINE GRIND SURFACE







## FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

SHAPE	S1 PLANO	\$2 PLANO	]			<b>Edmund</b>	Optics®
SURFACE FLATNESS	λ/2	λ/2	THIRD ANGLE	<u></u>	7171.5	25mm Dia., 5mm Thick	c, VIS-NIR Coated,
SURFACE QUALITY	40-20	40-20	PROJECTION PROJECTION		TITLE	Calcium Fluoride Window	
CLEAR APERTURE	Ø22.50	Ø22.50		'			0.1557
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	22602	SHEET 1 OF