
NOTES:

1. SUBSTRATE: VACUUM UV GRADE CaF2

- 2. SURFACE S2 TO BE PARALLEL WITH S1 TO < 1 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE) S1 & S2: R(ABS) ≤ 0.25% AT 880nm @ 0° AOI R(AVG) ≤ 1.25% FROM 400-870nm @ 0° AOI R(AVG) ≤ 1.25% FROM 890-1000nm @ 0° AOI

4. FINE GRIND SURFACE



## FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

## SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

- 1.00±0.10

-S2

/4\

S1-

	S1	\$2				<sup>©</sup> Edmund Optics <sup>®</sup>
SHAPE	PLANO	PLANO				
SURFACE FLATNESS	λ	λ				25.4mm Dia., 1mm Thick, VIS-NIR Coated,
SURFACE QUALITY	40-20	40-20	THIRD ANGLE		TITLE	Calcium Fluoride Window
CLEAR APERTURE	Ø22.86	Ø22.86		1		
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	22606 SHEET 1 OF 1