




NOTES:



- 1. SUBSTRATE:
VACUUM UV GRADE CaF2
- 2. SURFACE S2 TO BE PARALLEL WITH S1 TO < 1 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE)
S1 & S2: R(AVG) < 1% FROM 1650-3000nm @ 0° AOI
R(ABS) < 2% FROM 1650-3000nm @ 0° AOI

4. FINE GRIND SURFACE



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	 Edmund Optics®				
SHAPE	PLANO	PLANO					
SURFACE FLATNESS	λ	λ		TITLE	25.4mm Dia., 1mm Thick, BBAR (1650-3000nm) Coated, Calcium Fluoride Window		
SURFACE QUALITY	40-20	40-20					
CLEAR APERTURE	Ø22.86	Ø22.86					
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	22608	SHEET 1 OF 1