

## NOTES:

1. SUBSTRATE:
VACUUM UV GRADE CaF2

- 2. SURFACE S2 TO BE PARALLEL WITH S1 TO < 1 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE) \$1 & \$2: R(ABS) ≤ 0.25% AT 880nm @ 0° AOI R(AVG) ≤ 1.25% FROM 400-870nm @ 0° AOI R(AVG) ≤ 1.25% FROM 890-1000nm @ 0° AOI







## FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2	
SHAPE	PLANO	PLANO	
SURFACE FLATNESS	2λ	2λ	
SURFACE QUALITY	40-20	40-20	THIRD ANGLE PROJECTION
CLEAR APERTURE	Ø45.00	Ø45.00	
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN

				Edmund Optic	`C®
	THIRD ANGLE _ PROJECTION	$\phi \lhd$	TITLE	50mm Dia., 1mm Thick, VIS-NIR Coated, Calcium Fluoride Window	
D	ALL DIMS IN	mm	DWG NO	22610	SHEET 1 OF 1