NOTES:

1. SUBSTRATE:

Fused Silica

2. COATING (APPLY ACROSS CLEAR APERTURE) \$1: P-POLARIZATION TRANSMISSION EFFICIENCY: >98% \$-POLARIZATION REFLECTION EFFICIENCY: >99%

EXTINCTION RATIO: 10000:1


DAMAGE THRESHOLD, PULSED: 2J/cm² @ 532nm, 10ns, S or P Polarization


3. FINE GRIND SURFACE (ADD INK NOTE AS NEEDED)

4. POWER, IRREGULARITY, SURFACE QUALITY, AND COATING SPECIFICATIONS APPLY ACROSS CLEAR APERTURE

 $\sqrt{5.}$ APPLY ARROW ON EDGE WTH PENCIL OR PERMANENT INK TOWARDS S1

- 6. DESIGN WAVELENGTH: 532nm
- 7. ROHS COMPLIANT





FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	S1	\$2			
TRANSMITTED WAVEFRONT	λ/4 @ 633nm	λ/4 @ 633nm			[®] Edmund Optics [®]
ANGLE OF INCIDENCE (°)	45 ±2	45 ±2			
SHAPE	PLANO	PLANO			532nm, 50mm Diameter, Thin Film Laser Line
SURFACE QUALITY	40 - 20	40 - 20	THIRD ANGLE	TITLE	Beamsplitter
CLEAR APERTURE	Ø 45.00	Ø 45.00			
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED	ALL DIMS IN mm	DWG NO	21888 SHEET 1 OF 1

