

LightPath 354430 | 2mm Dia., 0.15 NA, BBAR (600-1050nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#48-145** **20+ In Stock**

⊖ 1 ⊕ **S\$136⁰⁵**

ADD TO CART

Volume Pricing	
Qty 1-10	S\$136.65 each
Qty 11-49	S\$120.22 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

354430 **Lightpath Lens Code:**

Aspheric Lens **Type:**

Typical Applications:
Collimate or Focus Laser Light

Physical & Mechanical Properties

Diameter (mm):
2.00 ±0.015

Clear Aperture CA (mm):
1.6

Edge Thickness ET (mm):
0.86

Center Thickness CT (mm):
1.01 ±0.05

Bevel:
Protective as needed

Optical Properties

Effective Focal Length EFL (mm):
5.00 @ 1550nm

Numerical Aperture NA:
0.15

Substrate:
[D-ZK3](#)

Focal Length Tolerance (%):
±1

Aspheric Design Wavelength (nm):
1550

Coating:
BBAR (600-1050nm)

Coating Specification:
R_{avg} <1.0% @ 600 - 1050nm

Surface Quality:
40-20

f#:
3.33

Wavelength Range (nm):
600 - 1050

Working Distance (mm):
4.37

Conjugate Distance:
Infinite

Transmitted Wavefront Error (λ, RMS):
< 0.17

Environmental & Durability Factors

Operating Temperature (°C):
≤200

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 247:
[Compliant](#)

PRODUCT DETAILS

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.

LASER OPTICS MADE BY EDMUND OPTICS®

[LEARN MORE](#)

TECHNICAL INFORMATION

