

LightPath 354057 | 6.33mm Dia., 0.20 NA, BBAR (350-700nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Stock **#83-685** CLEARANCE 3-5 DAYS
[Other Coating Options](#)

-

1

+

S\$33.28

ADD TO CART

Qty 1+
S\$33.28

Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
6.33 ±0.015

Effective Focal Length EFL (mm):
13.00 @633nm

Numerical Aperture NA:
0.20

Substrate: ☐
[D-ZK3](#)

Focal Length Tolerance (%):

±1
Aspheric Design Wavelength (nm): 633
Coating: BBAR (350-700nm)
Coating Specification: R _{avg} ≤0.5% @ 350 - 700nm
Surface Quality: 60-40
Clear Aperture CA (mm): 5.20
Edge Thickness ET (mm): 1.71
Center Thickness CT (mm): 2.38 ±0.05
f/#: 2.5
Bevel: Protective bevel as needed
Lightpath Lens Code: 354057
Type: Aspheric Lens
Wavelength Range (nm): 350 - 700
Working Distance (mm): 11.600
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant
