

[See all 77 Products in Family](#)

LightPath 354560 | 6.33mm Dia., 0.18 NA, BBAR (350-700nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#83-556** 20+ In Stock

-

1

+

S\$119^{.00}

ADD TO CART

Volume Pricing	
Qty 1-10	S\$119.00 each
Qty 11-49	S\$107.10 each
Need More?	Request Quote

Product Downloads

General

354560

Lightpath Lens Code:

Aspheric Lens

Type:

Collimate or Focus Laser Light

Typical Applications:

Physical & Mechanical Properties

6.33 ±0.015	Diameter (mm):
5.10	Clear Aperture CA (mm):
2.28	Edge Thickness ET (mm):
2.77 ±0.05	Center Thickness CT (mm):

Protective as needed	Bevel:
----------------------	--------

Optical Properties

13.90 @ 650nm	Effective Focal Length EFL (mm):
0.18	Numerical Aperture NA:

D-ZK3	Substrate: □
±1	Focal Length Tolerance (%):

650	Aspheric Design Wavelength (nm):
BBAR (350-700nm)	Coating:

R _{avg} <0.5% @ 350 - 700nm	Coating Specification:
40-20	Surface Quality:

2.78	f/#:
350 - 700	Wavelength Range (nm):

12.11	Working Distance (mm):
Infinite	Conjugate Distance:

< 0.07	Transmitted Wavefront Error (λ, RMS):
--------	---------------------------------------

Environmental & Durability Factors

≤200	Operating Temperature (°C):
------	-----------------------------


Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:


Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.



Technical Information



;