

[See all 77 Products in Family](#)

LightPath 354125 | 11mm Dia., 0.50 NA, BBAR (600-1050nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#33-426** **20+ In Stock**

[Other Coating Options](#)

-

1

+

S\$166⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	S\$166.60 each
Qty 11-49	S\$149.80 each
Need More?	Request Quote

Product Downloads


General	
Thickness: 0.25 (t) (mm) Material: B-K7	Compatible Window:
354125	Lightpath Lens Code:
Aspheric Lens	Type:

Typical Applications: Collimate or Focus Laser Light	
Physical & Mechanical Properties	
11.00 ±0.015	Diameter (mm):
10	Clear Aperture CA (mm):
1.092	Edge Thickness ET (mm):
3.64 ±0.40	Center Thickness CT (mm):
Protective as needed	Bevel:
Optical Properties	
10.00 @ 633nm	Effective Focal Length EFL (mm):
0.5	Numerical Aperture NA:
D-ZK3	Substrate: □
±1	Focal Length Tolerance (%):
633	Aspheric Design Wavelength (nm):
BBAR (600-1050nm)	Coating:
R _{abs} <1.0% @ 600 - 1050nm	Coating Specification:
60-40	Surface Quality:
1.00	f/#:
600 - 1050	Wavelength Range (nm):
7.8	Working Distance (mm):
Infinite	Conjugate Distance:
< 0.09	Transmitted Wavefront Error (λ, RMS):
Environmental & Durability Factors	
≤200	Operating Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.



Technical Information

