

0.50" Travel, 0.001" Grad, Micrometer Drive Mech



Drive Mechanisms

Stock #58-660 14 In Stock

-

1

+

S\$270²⁰

ADD TO CART

Volume Pricing	
Qty 1-9	S\$270.20 each
Qty 10-24	S\$243.18 each
Need More?	Request Quote

Product Downloads

General

English

Type:

PARKER-HANNIFIN

Manufacturer:

Physical & Mechanical Properties

0.5

Travel (inches):

Graduation (inches):

0.001	
	Stem Diameter (mm):
9.5	
	Stem/Spindle:
Plain/Flat	
	Stem Length (mm):
9.5	
	Spindle Diameter (mm):
6.6 (0.26")	
	Min. Spindle Length (mm):
6.35 (0.25")	
	Max. Diameter (mm):
13.7 (0.54")	
	Overall Length (mm):
60.5 (2.38")	

Hardware & Interface Connectivity

	Type of Drive:
English Micrometer	

Regulatory Compliance

	RoHS 2015:
Compliant	
	Certificate of Conformance:
View	

Product Details

- Micrometer, Fine Screw, Digital and Differential Options Available
 - Compatible with our [Ball Bearing Stages](#)
- These drive mechanisms add versatility to our selection of [ball bearing stages](#). Four options are available: micrometer (English and Metric), fine screw, digital, and differential. Please reference individual product descriptions to see which stages are compatible with each drive mechanism.

Technical Information

