

TECHSPEC® 0.5" Dia. Protected Aluminum, λ /10 Flat ZERODUR®



Stock **#43-327-522** 3-5 DAYS

- 1 + **S\$149.35**

ADD TO CART

Qty 1-10

S\$149.35

Qty 11+

S\$134.85

Volume Pricing

[Request Quote](#)

Get Product Downloads



Surface Flatness (P-V):
 λ /10 (measured before coating)

Back Surface:
Commercial Polish

Surface Quality: 60-40
Diameter (mm): 12.70 +0.0/-0.5
Substrate: 
Coating Specification: R _{avg} >85% @400 - 700nm R _{avg} >90% @400 - 2000nm
Coating: Protected Aluminum (400-2000nm)
Coating Type: Metal
Clear Aperture CA (mm): 11.43
Note: Flatness is specified as Peak to Valley
Thickness (mm): 3.20 ±0.8
Thickness Tolerance (mm): ±0.8
Type: Flat Mirror
Wavelength Range (µm): 0.4 - 2
Wavelength Range (nm): 400 - 2000
Damage Threshold, Reference:  0.3 J/cm ² @532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant